

Vetro

INSTALLATION CHECKLIST

GAGGIA
MILANO

Model	STANDARD Version		TALL Version	
	☐ 2 Groups	☐ 3 Groups	☐ 2 Groups	☐ 3 Groups
Dimensions (WxHxD)	28.7" x 18.5" x 20.9"	35.4" x 18.5" x 20.9"	28.7" x 20.5" x 20.9"	35.4" x 20.5" x 20.9"
Weight	100 lb	137 lb	100 lb	137 lb
Power Cord Plug	NEMA 6-20P	NEMA 6-30P	NEMA 6-20P	NEMA 6-30P
Max Absorbed Power	3700 W	4800 W	3700 W	4800 W
Voltage & Frequency	220 V / 60 Hz			

GENERAL MACHINE ENVIRONMENT

- ☐ The installation area is clean and clear of dust and tools. It is not located in an active construction zone.
- ☐ The counter accommodates the machine size and weight (check selected model).
- ☐ An access hole has been pre-drilled in the counter for drainage and power in accordance with model installation template.
- ☐ Hole in counter is fitted with a collar to protect electrical cord, water line & drain tube.
- ☐ Machine can safely be installed with minimum clearances of 3" from the back wall, 4" on each side and 12" on top.

ELECTRICAL REQUIREMENTS

- ☐ Power outlet receptacle is NEMA 6-20R (2 groups models) or NEMA 6-30R (3 groups models).
- ☐ Dedicated electrical circuit meets the selected Vetro model power requirements.
- ☐ No extension cord or power strip on the circuit.

WATER SPECIFICATIONS

Pressure & Hardness

- ☐ Pressure is between 44 PSI & 116.03 PSI.
- ☐ pH range is between 6.5 & 7.5.
- ☐ Hardness (TDS) is between 89 PPM & 142 PPM.
- ☐ Machine water line is equipped with softness/filtration system and descaling device.

Water Network

- ☐ The water network provides cold, drinkable tap water.
- ☐ Dedicated 3/8" diameter water line.
- ☐ Shutoff valve with a **3/8" G male pipe fitting** on machine's end.

HIGHLY RECOMMENDED: Connection to a floor drain in accordance with local health code.